




RoHS


VER	MARK	PR. BY	DESCRIPTION	DATE


Part No	Pin	A	B	C
HMT-FPC1.0-23-2P20H	2	1.00	3.10	6.90
HMT-FPC1.0-23-3P20H	3	2.00	4.10	7.90
HMT-FPC1.0-23-4P20H	4	3.00	5.10	8.90
HMT-FPC1.0-23-5P20H	5	4.00	6.10	9.90
HMT-FPC1.0-23-6P20H	6	5.00	7.10	10.90
HMT-FPC1.0-23-7P20H	7	6.00	8.10	11.90
HMT-FPC1.0-23-8P20H	8	7.00	9.10	12.90
HMT-FPC1.0-23-9P20H	9	8.00	10.10	13.90
HMT-FPC1.0-23-10P20H	10	9.00	11.10	14.90
.....		...		
HMT-FPC1.0-23-32P20H	32	(32-1)*1.0	(32+1)*1.0+0.10	(32+6)*1.0-0.10

序号	品名	材质
1	0.5 前翻胶芯 (H2.0)	LCP UL94V-0 本色
2	0.5 前翻端子 (H2.0)	铜合金 / 表面镀锡
3	0.5 前翻后盖 (H2.0)	LCP UL94V-0 黑色
4	0.5 前翻焊片 (H2.0)	铜合金 / 表面镀锡

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC/DC (等效)。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 500M\Omega$ 。



GENERAL TOLERANCES UNLESS SPECIFIED				 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd			
.X	±0.30	.X°	±5°	PART NO.	TITLE:		
.XX	±0.20	.XX°	±2°	HMT-FPC1.0-23-NP20H	1.0 Pitch 前翻卧式下接 (H=2.0)		
.XXX	±0.05	.XXX°	±1°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG				CHED: Talen		A4	MM
				APPD: Sophia		SCALE	SHEET
						N:A	1/1