








RoHs

| VER | MARK | PR. BY | DESCRIPTION | DATE |
|-----|------|--------|-------------|------|
|     |      |        |             |      |
|     |      |        |             |      |



| Part No              | Pin   | A          | B               | C               | D    |
|----------------------|-------|------------|-----------------|-----------------|------|
| HMT-FPC0.5-08-4P20H  | 4     | 1.50       | 2.56            | 7.60            |      |
| HMT-FPC0.5-08-5P20H  | 5     | 2.00       | 3.06            | 8.10            |      |
| HMT-FPC0.5-08-6P20H  | 6     | 2.50       | 3.56            | 8.60            |      |
| HMT-FPC0.5-08-7P20H  | 7     | 3.00       | 4.06            | 9.10            |      |
| HMT-FPC0.5-08-8P20H  | 8     | 3.50       | 4.56            | 9.60            |      |
| HMT-FPC0.5-08-9P20H  | 9     | 4.00       | 5.06            | 10.10           | 5.20 |
| HMT-FPC0.5-08-10P20H | 10    | 4.50       | 5.56            | 10.60           |      |
| HMT-FPC0.5-08-11P20H | 11    | 5.00       | 6.06            | 11.10           |      |
| HMT-FPC0.5-08-12P20H | 12    | 5.50       | 6.56            | 11.60           |      |
| .....                | ..... | .....      | .....           | .....           |      |
| HMT-FPC0.5-08-34P20H | 34    | 16.50      | 17.56           | 22.60           |      |
| HMT-FPC0.5-08-35P20H | 35    | 17.00      | 18.06           | 23.10           |      |
| HMT-FPC0.5-08-36P20H | 36    | 17.50      | 18.56           | 23.60           | 5.75 |
| .....                | ..... | .....      | .....           | .....           |      |
| HMT-FPC0.5-08-60P20H | 60    | (60-1)*0.5 | (60+1)*0.5+0.06 | (60+11)*0.5+0.1 |      |




| 序号 | 品名                | 材质             |
|----|-------------------|----------------|
| 1  | 0.5 拉拔胶芯 (H2.0)   | LCP UL94V-0 本色 |
| 2  | 0.5 拉拔下接端子 (H2.0) | 铜合金 / 表面镀锡     |
| 3  | 0.5 拉拔卧式后盖 (H2.0) | LCP UL94V-0 黑色 |
| 4  | 0.5 拉拔焊片 (H2.0)   | 铜合金 / 表面镀锡     |

适用扁平线 (Applicable Flat Cable)

适用线路板 (PCB LAYOUT)

- 技术指标:
- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
  - 温度范围:  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ 。
  - 额定电压: 50V, AC/DC。
  - 接触电阻:  $\leq 0.03\ \Omega$ 。
  - 绝缘电阻:  $\geq 500\text{M}\ \Omega$ 。

|                                        |       |       |     |                                                                                                                                                                                     |  |                                              |                                                                                       |       |
|----------------------------------------|-------|-------|-----|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|----------------------------------------------|---------------------------------------------------------------------------------------|-------|
| GENERAL TOLERANCES<br>UNLESS SPECIFIED |       |       |     | <div><div>深圳市华明通电子有限公司</div><div>HMTCONN Shenzhen Huamingtong Electronics Co., Ltd</div></div> |  |                                              |                                                                                       |       |
| .X                                     | ±0.30 | .X°   | ±5° | PART NO.                                                                                                                                                                            |  | TITLE:                                       |                                                                                       |       |
| .XX                                    | ±0.20 | .XX°  | ±2° | HMT-FPC0.5-08-NP20H                                                                                                                                                                 |  | 0.5 Pitch H2.0 ZIF R/A Type 3<br>Unper CONN. |                                                                                       |       |
| .XXX                                   | ±0.05 | .XXX° | ±1° | DESIGN: James                                                                                                                                                                       |  | CUSTOMER                                     | SIZE                                                                                  | UNITS |
| MANUFACTURE DWG                        |       |       |     | CHED: Talen                                                                                                                                                                         |  |                                              | A4                                                                                    | MM    |
|                                        |       |       |     | APPD: Sophia                                                                                                                                                                        |  |                                              |  | SCALE |
|                                        |       |       |     |                                                                                                                                                                                     |  |                                              | N:A                                                                                   | 1/1   |