








RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE



Part No	Pin	A	B	C
HMT-FPC1.0-08-4P25H	4	3.00	5.03	11.10
HMT-FPC1.0-08-5P25H	5	4.00	6.03	12.10
HMT-FPC1.0-08-6P25H	6	5.00	7.03	13.10
HMT-FPC1.0-08-7P25H	7	6.00	8.03	14.10
HMT-FPC1.0-08-8P25H	8	7.00	9.03	15.10
HMT-FPC1.0-08-9P25H	9	8.00	10.03	16.10
HMT-FPC1.0-08-10P25H	10	9.00	11.03	17.10
HMT-FPC1.0-08-11P25H	11	10.00	12.03	18.10
HMT-FPC1.0-08-12P25H	12	11.00	13.03	19.10
.....				
HMT-FPC1.0-08-40P25H	40	(40-1)*1.0	(40+1)*1.0+0.03	(40+6)*1.0+0.10




序号	品名	材质
1	1.0 胶芯 (H2.5)	LCP UL94V-0 本色
2	1.0 下接端子 (H2.5)	铜合金 / 表面镀锡
3	1.0 卧式后盖 (H2.5)	LCP UL94V-0 黑色
4	1.0 卧式焊片 (H2.5)	铜合金 / 表面镀锡

适用扁平线 (Applicable Flat Cable) 0.30 ± 0.03

适用线路板 (PCB LAYOUT)

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25° C ~ +85° C.
3. 额定电压: 50V, AC/DC.
4. 接触电阻: ≤ 0.03 Ω.
5. 绝缘电阻: ≥ 500M Ω

GENERAL TOLERANCES UNLESS SPECIFIED				 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd				
.X	±0.30	.X°	±5°	PART NO.		TITLE:		
.XX	±0.20	.XX°	±2°	HMT-FPC1.0-08-NP25H		1.0 Pitch H2.5 ZIF R/A Type Under CONN		
.XXX	±0.05	.XXX°	±1°	DESIGN: James		CUSTOMER	SIZE	UNITS
MANUFACTURE DWG				CHED: Talen			A4	MM
				APPD: Sophia			SCALE	SHEET
							N:A	1/1