








NOTES:

- MATERIAL:
 - HOUSING: THERMOPLASTIC, HIGH TEMP, UL94V-0, BLACK COLOR.
 - CONTACT: COPPER ALLOY.
- FINISH:
 - CONTACT: GOLD PLATING AT MATING AREA (SEE TABLE).G/F(1U"MIN) AT SOLDER TAIL, ALL OVER NICKEL 50U" MIN.
- FINISHED: ROHS 2.0 AND HF COMPLIANT;
- PART NO.:

M.2 40 53 - 05- R X X
40: 4.0 GEN 4
53: 5.3mm HEIGHT
FOR 0.5A
PACKING OPTIONS
R: TAPE & REEL
CONTACT AREA PLATING
2: G/F
C: 15u" Au
D: 30u" Au
KEY ID OPTIONS
B, E, M

				TOLERANCE		UMax 东莞市友贸实业有限公司 conn DONGGUAN UMAX ENTERPRISE LIMITED		TITLE: M.2 CONN. VERTICAL P=0.5, M KEY 5.3mm H, GEN4				
				LINEAR	ANGLES			PART NO. M.24053-05-RXX				
				X.±0.40	X°±							
				.X±0.30	.X°±	APPD: Jason	MAT'L:	DWG NO. C-M.24053-05				
1	-----	Yang Yiming	Jan,06,2024	.XX±0.20	.XX°±	CHKD: Schumi	FINISH:		UNITS	SCALE	SHEET	REV
REV	ECN NO.	NAME	DATE	.XXX±0.10	.XXX°±	DRWN:Lei Songping	Q'TY:					





CUSTOMER