






RoHS

Part No	PIN	A	B	C
HMT-MX1.25-CT2P	2	1.25	7.65	3.05
HMT-MX1.25-CT3P	3	2.50	8.90	4.30
HMT-MX1.25-CT4P	4	3.75	10.15	5.55
HMT-MX1.25-CT5P	5	5.00	11.40	6.80
HMT-MX1.25-CT6P	6	6.25	12.65	8.05
HMT-MX1.25-CT7P	7	7.50	13.90	9.30
HMT-MX1.25-CT8P	8	8.75	15.15	10.55
HMT-MX1.25-CT9P	9	10.00	16.40	11.80
HMT-MX1.25-CT10P	10	11.25	17.65	13.05
HMT-MX1.25-CT11P	11	12.50	18.90	14.30
HMT-MX1.25-CT12P	12	13.75	20.15	15.55
HMT-MX1.25-CT13P	13	15.00	21.40	16.80
HMT-MX1.25-CT14P	14	16.25	22.65	18.05
HMT-MX1.25-CT15P	15	17.50	23.90	19.30
HMT-MX1.25-CT16P	16	18.75	25.15	20.55

- NOTES:
- 1. BASE: PA6T
 - 2. PIN: Brass
 - 3. Solder Tab: Brass
- SPECIFICATIONS:
- 1. Spacing: 1.25
 - 2. Voltage Rating: 125V AC DC
 - 3. Current Rating: 1A AC DC
 - 4. Insulation Resistance: 100MΩ Min
 - 5. Contact Resistance: 20mΩ Max
 - 6. Withstanding voltage: 500V AC 1/Minute
 - 7. Temperatuer Range: -25℃ ~+ 85℃



GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.±0.20	X.°±5°	PART NO. HMT-MX1.25-CTNP	TITLE: WAFER 1.25 超薄	
.X±0.10	.X°±3°		CUSTOMER	SIZE A4
.XX±0.05	.XX°±1°	DESIGN: James		UNITS MM
MANUFACTURE DWG		CHED: Talen		SCALE
		APPD: Sophia		SHEET N:A 1/1