





RoHs



技术要求Specification:


- 1、材质Material: PA66 UL94V-0:
- 2、额定电流 Current rating:3.0A AC,DC
- 3、额定电压 Voltage rating:250V AC,DC
- 4、温度范围 Temperature range:-25℃to+85℃
- 5、接触电阻 Contact resistance: $\leq 20m\Omega$
- 6、绝缘电阻Insulation resistance: $\geq 1000M\Omega$
- 7、耐压Withstand voltage:1000V AC/minute
- 8、塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象.

Plastic surface smooth and clean, no obvious glitches, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.



VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table			
PART NO	PIN	A	B
HMT-HA2. 54-2Y-JK	2	2.50	5.80
HMT-HA2. 54-3Y-JK	3	5.00	8.30
HMT-HA2. 54-4Y-JK	4	7.50	10.80
HMT-HA2. 54-5Y-JK	5	10.00	13.30
HMT-HA2. 54-6Y-JK	6	12.50	15.80
HMT-HA2. 54-7Y-JK	7	15.00	18.30
HMT-HA2. 54-8Y-JK	8	17.50	20.80
.....			
HMT-HA2. 54-17Y-JK	17	40.00	43.30



GENERAL TOLERANCES UNLESS SPECIFIED		深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.X ± 0.30	X.° $\pm 5^\circ$	PART NO.	TITLE:	
.XX ± 0.20	X.X° $\pm 1^\circ$	HMT-HA2.54-NY-JK	HA2.5MM HOUSING	
.XXX ± 0.10	X.XX° $\pm 0.5^\circ$	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia	SCALE	SHEET
			N:A	1/1