





RoHS

| VER | MARK | PR. BY | DESCRIPTION | DATE |
|-----|------|--------|-------------|------|
|     |      |        |             |      |
|     |      |        |             |      |



| PIN number variable size comparison table |       |       |       |       |
|-------------------------------------------|-------|-------|-------|-------|
| PART NO                                   | PIN   | A     | B     | C     |
| HMT-XH2.54-LT2P                           | 2     | 2.50  | 10.00 | 7.50  |
| HMT-XH2.54-LT3P                           | 3     | 5.00  | 12.50 | 10.00 |
| HMT-XH2.54-LT4P                           | 4     | 7.50  | 15.00 | 12.50 |
| HMT-XH2.54-LT5P                           | 5     | 10.00 | 17.50 | 15.00 |
| HMT-XH2.54-LT6P                           | 6     | 12.50 | 20.00 | 17.50 |
| .....                                     | ..... | ..... | ..... | ..... |
| HMT-XH2.54-LT16P                          | 16    | 37.50 | 45.00 | 42.50 |




NOTES:


1. BASE: LCP
2. PIN: Brass
3. Solder Tab: Brass

SPECIFICATIONS:

1. Spacing: 2.5
2. Voltage Rating: 250V AC DC
3. Current Rating: 3A AC DC
4. Insulation Resistance: 800MΩ Min
5. Contact Resistance: 20mΩ Max
6. Withstanding voltage: 1000V AC 1/Minute
7. Temperature Range: -25℃ ~+ 85℃



2PIN结构



| GENERAL TOLERANCES<br>UNLESS SPECIFIED |             | 深圳市华明通电子有限公司<br>HMTCONN Shenzhen Huamingtong Electronics Co., Ltd |                         |            |             |
|----------------------------------------|-------------|-------------------------------------------------------------------|-------------------------|------------|-------------|
| X.X ±0.30                              | X.* ±5°     | PART NO.<br>HMT-XH2.54-LTNP                                       | TITLE:<br>WAFER 2.54 立贴 |            |             |
| .XX ±0.20                              | X.X* ±1°    |                                                                   |                         |            |             |
| .XXX ±0.10                             | X.XX* ±0.5° | DESIGN: James                                                     | CUSTOMER                | SIZE<br>A4 | UNITS<br>MM |
| MANUFACTURE DWG                        |             | CHED: Talen                                                       |                         | SCALE      | SHEET       |
|                                        |             | APPD: Sophia                                                      |                         | N:A        | 1/1         |