




RoHS

VER	MARK	PR. BY	DESCRIPTION	DATE

Part No	Pin	A	B	C
HMT-FPC1.0-07-4P25H	4	3.00	5.03	11.10
HMT-FPC1.0-07-5P25H	5	4.00	6.03	12.10
HMT-FPC1.0-07-6P25H	6	5.00	7.03	13.10
HMT-FPC1.0-07-7P25H	7	6.00	8.03	14.10
HMT-FPC1.0-07-8P25H	8	7.00	9.03	15.10
HMT-FPC1.0-07-9P25H	9	8.00	10.03	16.10
HMT-FPC1.0-07-10P25H	10	9.00	11.03	17.10
HMT-FPC1.0-07-11P25H	11	10.00	12.03	18.10
HMT-FPC1.0-07-12P25H	12	11.00	13.03	19.10
.....		...		
HMT-FPC1.0-07-40P25H	40	(40-1)*1.0	(40+1)*1.0+0.03	(40+6)*1.0+0.10

序号	品名	材质
1	1.0 胶芯 (H2.5)	LCP UL94V-0 本色
2	1.0 上接端子 (H2.5)	铜合金 / 表面镀锡
3	1.0 卧式后盖 (H2.5)	LCP UL94V-0 黑色
4	1.0 卧式焊片 (H2.5)	铜合金 / 表面镀锡

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
3. 额定电压: 50V, AC/DC.
4. 接触电阻: $\leq 0.03\ \Omega$.
5. 绝缘电阻: $\geq 500M\ \Omega$

GENERAL TOLERANCES UNLESS SPECIFIED		HMTconn 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
.X	± 0.30	.X°	$\pm 5^{\circ}$	PART NO.
.XX	± 0.20	.XX°	$\pm 2^{\circ}$	HMT-FPC1.0-07-NP25H
.XXX	± 0.05	.XXX°	$\pm 1^{\circ}$	DESIGN: James
MANUFACTURE DWG		CHED: Talen	APPD: Sophia	TITLE: 1.0 Pitch H2.5 ZIF R/A Type Top CONN.
				CUSTOMER
				SIZE
				UNITS
				SCALE
				SHEET