




Current Rating:	1.0 Amps
Withstanding Voltage:	AC 500V
Insulation Resistance:	1000M Ω Min
Contact Resistance:	20m Ω Max
Operation Temperature:	-40° to+105°
Insrlator Material:	Polyester (UL94V-0)
Contact Material:	Brass
Standard:	PA6T
Contact Plating:	Gold Flash
Max.Processing Temp:	240° C for30-60seconds (260° C for5seconds)




P/N	PIN	$DIM. A$	$DIM. B$
$HMT-PZ1.27-1-1PZ$	1	0.00	1.27
$HMT-PZ1.27-1-2PZ$	2	1.27	2.54
$HMT-PZ1.27-1-3PZ$	3	2.54	3.81
$HMT-PZ1.27-1-4PZ$	4	3.81	5.08
$HMT-PZ1.27-1-5PZ$	5	5.08	6.35
$HMT-PZ1.27-1-6PZ$	6	6.35	7.62
$HMT-PZ1.27-1-7PZ$	7	7.62	8.89
$HMT-PZ1.27-1-8PZ$	8	8.89	10.16
$HMT-PZ1.27-1-9PZ$	9	10.16	11.43
.....			
$HMT-PZ1.27-1-50PZ$	50	$(PIN-1)_{x1.27}$	$(PIN)_{x1.27}$



RECOMMEND P. C. B LAYOUT

PCB TOLERANCE: ± 0.05 (TOP VIEW)

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.° ±0.30	X.° ±5°	PART NO.	TITLE:		
X.X° ±0.20	X.X° ±1°	HMT-PZ1.27-1-NPZ	1.27PH H1.0 1xnPin 180度 W2.0 PC2.3 PA3.9 PB1.0 L7.2 6T 0.4#		
X.XX°±0.10	X.XX°±0.5°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1