

RoHs






VER	MARK	PR. BY	DESCRIPTION	DATE

NOTES:


1. BASE: LCP
2. PIN: Brass
3. Solder Tab: Brass

SPECIFICATIONS:

1. Spacing: 2.5
2. Voltage Rating: 250V AC DC
3. Current Rating: 3A AC DC
4. Insulation Resistance: 800M Ω Min
5. Contact Resistance: 20m Ω Max
6. Withstanding voltage: 1000V AC 1/Minute
7. Temperatuer Range: -25 $^{\circ}$ C ~+ 85 $^{\circ}$ C



PIN number variable size comparison table				
PART NO	PIN	A	B	C
HMT-HA2.54-LT2P	2	2.50	10.00	7.50
HMT-HA2.54-LT3P	3	5.00	12.50	10.00
HMT-HA2.54-LT4P	4	7.50	15.00	12.50
HMT-HA2.54-LT5P	5	10.00	17.50	15.00
HMT-HA2.54-LT6P	6	12.50	20.00	17.50
HMT-HA2.54-LT7P	7	15.00	22.50	20.00
.....				
HMT-HA2.54-LT16P	16	37.50	45.00	42.50



GENERAL TOLERANCES
UNLESS SPECIFIED

X.X	±0.30	X. $^{\circ}$	±5 $^{\circ}$
.XX	±0.20	X.X $^{\circ}$	±1 $^{\circ}$
.XXX	±0.10	X.XX $^{\circ}$	±0.5 $^{\circ}$

MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
HMT-HA2.54-LTNP

DESIGN: James
CHED: Talen
APPD: Sophia

TITLE:
WAFER XHB2.54 立贴带扣

CUSTOMER	SIZE	UNITS
	A4	MM
	SCALE	SHEET
	N:A	1/1