





技术参数:
PIN数: 2~12
适用线规: AWG22#~18#
适用基板厚度: 1.6mm
温度范围: -25℃~85℃
额定电压: 250V AC/DC
额定电流: 7.5A
接触电阻: ≤0.015 Ω
绝缘电阻: ≥1000N Ω
耐压: 1500V AC/minute
材料: (Nylon)66UL94V-2(0)

PIN number variable size comparison table			
PART NO	PIN	A	B
HMT-VH3. 96-2Y-JK	2	3.96	8.07
HMT-VH3. 96-3Y-JK	3	7.92	12.03
HMT-VH3. 96-4Y-JK	4	11.88	15.99
HMT-VH3. 96-5Y-JK	5	15.84	19.95
HMT-VH3. 96-6Y-JK	6	19.80	23.91
HMT-VH3. 96-7Y-JK	7	23.76	27.87
HMT-VH3. 96-8Y-JK	8	27.72	31.83
HMT-VH3. 96-9Y-JK	9	31.68	35.79
HMT-VH3. 96-10Y-JK	10	35.64	39.75
HMT-VH3. 96-11Y-JK	11	39.60	43.71
HMT-VH3. 96-12Y-JK	12	43.58	47.67

GENERAL TOLERANCES UNLESS SPECIFIED		HMTconn 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.X ±0.30	X.° ±5°	PART NO.	TITLE: VH3.96MM HOUSING	
.XX ±0.20	X.X° ±1°	HMT-VH3.96-NY-JK		
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE UNITS
		CHED: Talen		A4 MM
MANUFACTURE DWG		APPD: Sophia	SCALE	SHEET
			N:A	1/1