









VER	MARK	PR. BY	DESCRIPTTON	DATE



Part No	Pin	A	B	C
HMT-FPC0. 5-23-4P20H	4	1. 50	2. 60	6. 40
HMT-FPC0. 5-23-5P20H	5	2. 00	3. 10	6. 90
HMT-FPC0. 5-23-6P20H	6	2. 50	3. 60	7. 40
HMT-FPC0. 5-23-7P20H	7	3. 00	4. 10	7. 90
HMT-FPC0. 5-23-8P20H	8	3. 50	4. 60	8. 40
HMT-FPC0. 5-23-9P20H	9	4. 00	5. 10	8. 90
HMT-FPC0. 5-23-10P20H	10	4. 50	5. 60	9. 40
HMT-FPC0. 5-23-11P20H	11	5. 00	6. 10	9. 90
HMT-FPC0. 5-23-12P20H	12	5. 50	6. 60	10. 40
.....		...		
HMT-FPC0. 5-23-65P20H	65	(60-1)*0. 5	(60+1)*0. 5+0. 10	(60+9)*0. 5-0.



SECTION A-A




适用线路板 (PCB LAYOUT)

适用扁平线 (Applicable Flat Cable)

序号	品名	材质
1	0.5 前翻胶芯 (H=2.0)	LCP UL94V-0 本色
2	0.5 前翻端子 (H=2.0)	铜合金 / 表面镀锡
3	0.5 前翻后盖 (H=2.0)	LCP UL94V-0 黑色
4	0.5 前翻焊片 (H=2.0)	铜合金 / 表面镀锡

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ 。
3. 额定电压: 50V , AC/DC。
4. 接触电阻: $\leq 0.03\ \Omega$ 。
5. 绝缘电阻: $\geq 500\text{M}\Omega$ 。



GENERAL TOLERANCES UNLESS SPECIFIED		HMT CONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
.X ±0.30	.X° ±5°	PART NO.		TITLE:	
.XX ±0.20	.XX° ±2°	HMT-FPC0.5-23-NP20H		0.5 Pitch H2.0 Easy-on R/A Down Type CONN	
.XXX ±0.05	.XXX° ±1°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/2

