

1

2

3

4

5

6

7

8

项目 Mapx	设 变 内 容 Modification	日 期 Date	修改人 Draw	核 准 Approve

A





B

C

D

E

F



规格说明 Specifications:

电气特性 Electrical:

1. 额定电流: Current Rating
3.0A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触电阻 Contact Resistance
30 milliohms MAX
4. 耐电压 Dielectric Withstanding Voltage:
500 V AC AT Sea Level
5. 绝缘电阻 Insulation Resistance:
1000MEGA ohms MIN

物理性能 Mechanical:

1. 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf<MAX>
Unmate force: 1.02kgf<MIN>

原材料 Material:

1. 塑胶 Housing:
Hing Temperature Tnermaplastics,
2. 端子 Contact: Copper Alloy C2680
3. 外壳 Shell: Copper Alloy C2680/SPCC

A

B

C

D

E

F

AUTODESK

成品图 MANUFACTURE DWG		东莞市文章济美电子有限公司									
公差一览表 TOLERANCE UNLESS OTHERWISE											
.X±0.20	X.±5°	日期 DATE	2016.10.20	单位 UNIT	MM	制图 DRAWING		DWG NO.			
XX±0.10	.X±2°	审核 CHECKED		SCALE	1 : 1	设计 DESIGN	LIUFU	品 名 NAME	USB-2.0AF 90DU-B		
XXX±0.05	.XX±1°	核准 APPROVE		角法 VIEW	⊕ ⊖			版 本 VER	AO	页 数 SHEET	011

1

2

3

4

5

6

7

8