

项目 Mapx	设计内容 Modification	日期 Date	修改人 Draw	核准 Approve

规格说明: Specifications:

电气特性: Electrical:

- 1.额定电流: Current Rating
1.5A/contact terminal
- 2.额定电压: Voltage Rating
30V DC
- 3.接触电阻: Contact Resistance
30 milliohms MAX
- 4.耐电压: Dielectric Withstanding Voitage:
500 V AC AT Sea Level
- 5.绝缘电阻: Lnsulation Resistance:
1000MEGA ohms MIN

物理性能: Mechanical:

- 1.插拔力: Cnncector Mate and Unmate Force
Mate force:3.57kgf(MAX)
Unmate force:1.02kgf(MIN)
- 2.端子保持力: Terminal Retenion
1.0kgf(MIN)

原材料: Material:

- 1.塑胶: Housing:
Hing Temperature Tnermaplastics,
- 2.端子: Contact: Copper Alloy C2680
- 3.外壳: Shell: Copper Alloy C2680/SPCC

电镀: Finish:

- 1.端子: Contact: Plated Gold in Mating Area,
Tin On Solder Talls
端子四周镀30—50U”(MIN)锡,镀金区域镀金1U”
- 2.外壳: Shell:
铜—铁壳四周镀50—80U”(MIN)镍

Nickel Plating

成品图 MANUFACTURE DWG		东莞市文章济美电子有限公司									
公差—毫米 TOLERANCE UNLESS OTHERWISE		日期 DATE	2016.10.20	单位 UNIT	MM	制图 DRAWING		DWG NO.			
.X±0.15	.X.±5°	审核 CHECKED		比例 SCALE	1:1	设计 DESIGN	LIUFU	品名 NAME	USB-2.0AFZC15.1-B		
.XX±0.05	.X.±2°	核准 APPROVE		画法 VIEW	第一角 VIEW			版本 VER	AO	页数 SHEET	PG1
.XXX±0.02	.XX.±1°										

