

RoHS Compliant

REV.	MODIFICATION	ECN No.	NAME	DATE
A0	NEW		LEN.SONG	2022.01.05

NOTES:









- CURRENT RATING:
3.0A MAX.
- DIELECTRIC WITHSTAND VOLTAGE:
100VAC.
- TEMPERATURE RANGE:
-30 °C ~ 85 °C.
- CONTACT RESISTANCE:
40 MILLIONHM MAX.
- INSULATION RESISTANCE:
100 MEGOHMS MIN.
- INSERTION FORCE :
5N~20N.
- UNMATING FORCE:
8N~20N.
- DURABILITY:
10,000 CYCLES.
- WATERPROOF RATING: **IPX7**.
- ALL PRODUCTS COMPLY WITH RoHS ENVIRONMENTAL REQUIREMENTS.
- MARK "▼" AS THE FOCUS, FIRST ITEM INSPECTION.
- MARK "⊗" TO MEASURE DIMENSIONS FOR FAI.

TABLE:

A180203111046	环氧树脂			PK13001				
	外壳			S1846A007	SUS304R-1/2H,T=0.20mm	Ni:50u"Min;		
	内壳			S1846A508	SUS304R-1/2H,T=0.30mm	Ni:50u"Min;		
	护套			H18020301010	PA9T(G,F30%),BLACK.			
	MD 半成品 B180203111008	中夹片		S18428003	SUS301R-HLT=0.15mm	／		
		上排MD	B180203111009	端子: T18118015 SY11034001	C2808R-HLT=0.15mm	Ni:30u"Min; Au:CONTACT AREA=1u" Solder AREA=MATTE-Tin.		
		下排MD	B180203111010	端子: T18118017 SY11034001	C2808R-HLT=0.15mm			
		塑胶		SY11034001	LOP(G,F30R) BLACK.	／		
		P/N			PART NAME	P/N	MATERIALS	FINISH


东莞市文章济美电子有限公司

.X: ±0.35	.X*: ±5.0°	INTENDED USE:	TITLE: Type-C-16P-SJFS-B	
.XX: ±0.25	.XX*: ±3.0°	CUSTOMER DRAWING	PART NO.:	SEE TABLE
.XXX: ±0.15	.XXX*: ±1.5°	APPD.:	DWG. NO.:	T16-000X
MAT'L.: SEE NOTES		CHKD.:	SCALE: 1:1	PAGE: 1/1
FINISH:		DR.: JIMI	UNIT: mm	REV.: A0



A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SUB1	VBUS			GND
GND			VBUS	SUB2	D-	D+	CC1	VBUS			GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

防水圈:



- 材料: 黑色硅胶, 符合ROHS环境管理物质.
- 尺寸: 外径: 10.64*4.86*1.50mm.