







PART NUMBER DESCRIPTION:

RJ45-401-013-XX

流水码

32:有壳左绿右黄B3.85 GF PA46黑塑壳

PA46内芯盘装

NOTES

MATERIAL

- | | |
|---------------------|--|
| 1. HOUSING MATERIAL | : PA46 BLACK UL94V-0. |
| 2. CONTACT MATERIAL | : PHOSPHOR BRONZE $\phi 0.46\text{mm}$. |
| 3. PLATING | : GOLD FLASH PLATING. |
| 4. SHELL: | : BRASS T=0.2mm NI PLATING. |

ELECTRICAL


- | | |
|-------------------------------------|------------------------------|
| 1. VOLTAGE RATING | : 125 VAC RMS. |
| 2. CURRENT RATING | : 1.5 AMP. |
| 3. CONTACT RESISTANCE | : 40 MILLIOHMS MAX. |
| 4. INSULATION RESISTANCE | : 500 MEGOHMS MIN @ 100V DC. |
| 5. DIELECTRIC DIELECTRIC RESISTANCE | : 500V DC RMS 50Hz. 1MIN. |

MECHANICAL

- | | |
|--------------------------|-------------------|
| 1. DURRABILITY | : 750 CYCLES MIN. |
| 2. MATING/UNMATING FORCE | : 2.24 KG.F MAX. |

ENVIRONMENTAL:

- | | |
|--------------|--------------|
| 1. STORAGE | : -40℃~+85℃. |
| 2. OPERATION | : -40℃~+85℃. |



PCBLAYOUT

TOL:±0.05

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co., LtdUNLESS OTHERWISE
SPECIFIED TOLERANCESTITLE:RJ45 52立式有壳左绿右黄
B3.85 DIP

PAR RJ45-401-013-32

DWN Lucas

CHKD Ethan

APVD Jacob

SCALE:1:1 UNIT:MM

SIZE:A4 SHEET:1F1



DECIMALS:

ANGLES:

.X:±0.35

X.:±3°

.XX:±0.25

X.X:±2°

.XXX:±0.15

X.XX:±1°

CUSTOMER COPY

REV:A