




项目 Mapx	设计内容 Modification	日期 Date	修改人 Draw	核准 Approve

规格说明:Specifications:

电气特性:Electrical:

PIN NU_BER	SIGNAL NAME
1	USB 电压
2	D-(负极)
3	D+(正极)
4	地线
5	SSRX-
6	SSRX+
7	GND(地线)
8	SSTX-
9	SSTX+
shell	SHIELD

- 1.额定电流: Current Rating
- 1.5A/contact terminal
- 2.额定电压: Voltage Rating
- 30V DC
- 3.接触阻抗:Contact Resistance
- 30 milliohms MAX
- 4.耐电压:Dielectnic Withstanding Voitage:
- 500 V AC AT Sea Level
- 5.绝缘阻抗:Lnsulation Resistance:
- 1000MEGA ohms MIN

物理性能:Mechanical:

- 1.插拔力: Cnnector Mate and Unmate Force
- Mate force:3.57kgf(MAX)
- Unmate force:1.02kgf(MIN)

原材料:Material:

- 1.塑胶:Housing:
- Hing Temperature Tnermaplastics,
- 2.端子:Contact:Copper Alloy C2680
- 3.外壳:Shell: SPCC

1.端子:Contact: Plated Gold in Mating Area

电镀:Finish: Tin On Solder Talls

端子四周镀60U”(MIN)-100U锡,”镀金1U”

- 2.外壳:Shell:
- 外壳四周镀60U”(MIN)镍
- Nickel Plating

成品图 MANUFACTURE DWG		东莞市文章济美电子有限公司									
公差一览表 TOLERANCE UNLESS OTHERWISE		日期 DATE	2023.04.27	单位 UNIT	MM	制图 DRAWING		DWG NO.			
.X±0.20	.X±5°	审核 CHECKED		比例 SCALE	1 : 1	设计 DESIGN	LIUFU	品名 NAME	USB-3.0AF-CBSCBL14.2-B		
XXX±0.02	.XX±1°	核准 APPROVE		角法 VIEW				版本 VER	AO	页数 SHEET	001

RECOMMENDED PCBA LAYOUT
(TOLERANCE+ ± 0.05)