




P/N	CKT	A	B	C	D	E
JME123040-602050-HF	20	4.50	9.50	18.16	15.70	20.96
JME123040-603050-HF	30	7.00	12.00	20.66	18.20	23.46
JME123040-604050-HF	40	9.50	14.50	23.16	20.70	25.96
JME123040-605050-HF	50	12.00	17.00	25.66	23.20	28.46
JME123040-606050-HF	60	14.50	19.50	28.16	25.70	30.96
JME123040-608050-HF	80	19.50	24.50	33.16	30.70	35.96
JME123040-600050-HF	100	24.50	29.50	38.16	35.70	40.96
JME123040-600250-HF	120	29.50	34.50	43.16	40.70	45.96

NOTES:
1. "▲" means Key dimentions, "△" means Important dimensions.
2. PART NO. Specifications : JME123040-60XX50-HF
XX: Code of signal contact quantity

5	Hook	2	Copper alloy	Under: Ni 50~100u'', Tail: Tin 80~150u''
4	Power contact	4	Copper alloy	Under: Ni 60~200u'', Contact: Au 4u'' Min, Tail: Tin 80~150u''
3	Signal contact	Pin number	Copper alloy	Under: Ni 60~200u'', Contact: Au 4u'' Min, Tail: Au 2u'' Min.▲
2	CAP	1	LCP, UL94V-0, Black	N/A
1	Insulator	1	LCP, UL94V-0, Black	N/A
No.	Part name	Quantity	Material	Plating

△	Correction update	GY.CEN	2022-10-27	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
△	Correction update	QF.DONG	2022-10-27	X. ±0.20
△	Correction update	QF.DONG	2022-07-15	X.XX ±0.10
△	Correction update	QF.DONG	2022-07-01	X.XXX
△	Change the tol	Kuan He	2022-03-02	ANG. ±0°30'
	New released	Kuan He	2022-02-10	UNIT
SER	REVISIONS	CHK	DATE	MM

客户图 Drawings	东莞市文章济美电子有限公司			
APPROVED TS Chen	DATE 2022-02-10	COMPUTER NO JME123040-60XX50-HF		
CHECKED QF DONG	DATE 2022-02-10	NAME BTB0.5-5B REC (THR TYPE) Page 1/2		
DRAWN Kuan He	DATE 2022-02-10	SIZE A4	SCALE 2:1	REV E

