








技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 工作温度: -40°C~105°C.
3. 适用线规: AWG#28~#22.
4. 额定电压: 250V DC/AC(rms).
5. 额定电流: 3.0A AC, DC.
6. 接触电阻: ≤20mΩ.
7. 耐压值: 800V AC/minute.
8. 绝缘电阻: ≥1000MΩ.

1	2.0A型双排立式WTB胶芯	LCP UL94V-0 本色
2	2.0A型双排卧式短端子	铜合金/表面镀锡
3	2.0A型双排卧式长端子	铜合金/表面镀锡
序号	名称	材质

型号	CKT	A	B	C
WAfer-PHB2.0-4PWB-GM	2*2	2.00	6.00	3.20
WAfer-PHB2.0-6PWB-GM	2*3	4.00	8.00	3.20
WAfer-PHB2.0-8PWB-GM	2*4	6.00	10.00	3.00
WAfer-PHB2.0-10PWB-GM	2*5	8.00	12.00	5.00
WAfer-PHB2.0-12PWB-GM	2*6	10.00	14.00	7.00
WAfer-PHB2.0-14PWB-GM	2*7	12.00	16.00	9.00
WAfer-PHB2.0-16PWB-GM	2*8	14.00	18.00	11.00
WAfer-PHB2.0-18PWB-GM	2*9	16.00	20.00	13.00
WAfer-PHB2.0-20PWB-GM	2*10	18.00	22.00	15.00
WAfer-PHB2.0-22PWB-GM	2*11	20.00	24.00	17.00
WAfer-PHB2.0-24PWB-GM	2*12	22.00	26.00	19.00
WAfer-PHB2.0-26PWB-GM	2*13	24.00	28.00	21.00
WAfer-PHB2.0-28PWB-GM	2*14	26.00	3.00	23.00
WAfer-PHB2.0-30PWB-GM	2*15	28.00	32.00	25.00
WAfer-PHB2.0-32PWB-GM	2*16	30.00	34.00	27.00
WAfer-PHB2.0-36PWB-GM	2*18	34.00	38.00	31.00
WAfer-PHB2.0-40PWB-GM	2*20	38.00	42.00	35.00
WAfer-PHB2.0-44PWB-GM	2*22	42.00	46.00	39.00

适用线路板(PCB LAYOUT)

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: 2.0 Pitch A型双排卧式WTB	
DECIMALS: X.:±0.50 X.X:±0.20 X.XX:±0.10		PAR WAfer-PHB2.0-NPWB-GM	
ANGLES: ±1°		DWN Lucas	
		CHKD Ethan	
		APVD Jacob	
		SCALE:1:1	
		UNIT:MM	
		SIZE:A4	
		SHEET:1F1	
		REV:A	