







适用线路板(PCB Layout)

技术指标(Technical Index):

- 1.工作温度(Temperature range):
-40°C~+105°C.
- 2.额定电压(Rated voltage):250V DC/AC(rms).
- 3.额定电流(Rated current):3.0A AC,DC.
- 4.接触电阻(Contact resistance):≤20mΩ.
- 5.耐压值(Dielectricwithstanding voltage):
800V AC/minute.
- 6.绝缘电阻(Insulation resistance):≥1000MΩ.

序号	品名	材质
①	PHD2.0弯针WTB胶芯	PA66加玻纤
②	PHD2.0弯针WTB端子	UL94 V-0 米色
		铜合金/表面镀锡

Part No	CKT	A	B
PHD2.0-02-4PWZ	2*2	2.0	6.0
PHD2.0-02-6PWZ	2*3	4.0	8.0
PHD2.0-02-8PWZ	2*4	6.0	10.0
PHD2.0-02-10PWZ	2*5	8.0	12.0
PHD2.0-02-12PWZ	2*6	10.0	14.0
PHD2.0-02-14PWZ	2*7	12.0	16.0
PHD2.0-02-16PWZ	2*8	14.0	18.0
PHD2.0-02-18PWZ	2*9	16.0	20.0
PHD2.0-02-20PWZ	2*10	18.0	22.0
PHD2.0-02-22PWZ	2*11	20.0	24.0
PHD2.0-02-24PWZ	2*12	22.0	26.0
PHD2.0-02-26PWZ	2*13	24.0	28.0
PHD2.0-02-28PWZ	2*14	26.0	30.0
PHD2.0-02-30PWZ	2*15	28.0	32.0
PHD2.0-02-32PWZ	2*16	30.0	34.0
PHD2.0-02-34PWZ	2*17	32.0	36.0
PHD2.0-02-36PWZ	2*18	34.0	38.0
PHD2.0-02-38PWZ	2*19	36.0	40.0
PHD2.0-02-40PWZ	2*20	38.0	42.0

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:

X.:±0.50

X.X:±0.20

X.XX:±0.10

ANGLES:

±1°



TITLE:

PHD2.0 弯针WTB

PAR

PHD2.0-02-NPWZ

DWN

Lucas

CHKD

Ethan

APVD

Jacob

SCALE:1:1

UNIT:MM

SIZE:A4

SHEET:1F1

REV:A