






SECTION A-A



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$.
3. 额定电压: 30V, AC/DC.
4. 耐电压: 200V, AC/minute.
5. 接触电阻: $\leq 0.02\Omega$.
6. 绝缘电阻: $\geq 100\text{M}\Omega$.
7. 额定电流: 0.5A AC/DC.

序号	品名	材质
①	0.6—卧式WTB胶芯	LCP UL94 V-0 黑色
②	0.6—卧式WTB端子	铜合金/表面镀锡
③	0.6—卧式WTB焊片	铜合金/表面镀锡



Part No	CKT	A	B	C
WAFER-0.6-2PWT	2	0.60	1.40	3.10
WAFER-0.6-3PWT	3	1.20	2.00	3.70
WAFER-0.6-4PWT	4	1.80	2.60	4.30
WAFER-0.6-5PWT	5	2.40	3.20	4.90
WAFER-0.6-6PWT	6	3.00	3.80	5.50
WAFER-0.6-7PWT	7	3.60	4.40	6.10
WAFER-0.6-8PWT	8	4.20	5.00	6.70
WAFER-0.6-9PWT	9	4.80	5.60	7.30
WAFER-0.6-10PWT	10	5.40	6.20	7.90
WAFER-0.6-11PWT	11	6.00	6.80	8.50
WAFER-0.6-12PWT	12	6.60	7.40	9.10
WAFER-0.6-13PWT	13	7.20	8.00	9.70
WAFER-0.6-14PWT	14	7.80	8.60	10.30
WAFER-0.6-15PWT	15	8.40	9.20	10.90
WAFER-0.6-16PWT	16	9.00	9.80	11.50
WAFER-0.6-17PWT	17	9.60	10.40	12.10
WAFER-0.6-18PWT	18	10.20	11.00	12.70
WAFER-0.6-19PWT	19	10.80	11.60	13.30
WAFER-0.6-20PWT	20	11.40	12.20	13.90
WAFER-0.6-21PWT	21	12.00	12.80	14.50
WAFER-0.6-22PWT	22	12.60	13.40	15.10

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCES

TITLE:

0.60 Pitch 卧式WTB

PAR

WAFER-0.6-NPWT

DWN

Lucas

CHKD

Ethan

APVD

Jacob

SCALE:1:1

UNIT:MM

SIZE:A4

SHEET:1F1

REV:A

CUSTOMER COPY