





Model No.	POS.1	POS.2	POS.3
			
2AS3	ON	OFF	ON
Term. Comm.	2-3	OPEN	2-1
SCHEMATIC			

SWITCH FUNCTION



P.C. MOUNTING

SPECIFICATIONS

MECHANICAL LIFE: 50,000 make-and-break cycles.

CONTACT RESISTANCE: 20mΩ max. initial @ 2-4VDC
100mA for both silver and gold plated contacts.

INSULATION RESISTANCE: 1,000MΩ min.

DIELECTRIC STRENGTH: 1,000 V RMS@sea level.

OPERATING TEMPERATURE: -30°C to 85°C.

MATERIALS

CASE & BUSHING - Glass filled nylon 6/6 , retardant ,
heat stadilized(UL94V-0)

ACTUATOR - Brass, chrome platede.Internal O-ring seal. standard
for all actuators.

SWITCH SUPPORT - Brass , tin plated.

TERMINALS/CONTACT - Silver or gold plated copper.

RATING :

R : 0.4 Volt-Amps(VA) max. @20V max.(AC or DC)

Q : 1Amp @250VAC

3Amps @120 VAC or 28 VDC

东莞市弘皓电子有限公司

	符號	原尺寸	修改後尺寸	變更日期	SCALE (比例) : 3 : 2	TITLE 圖 名	Sealed Sub - Miniature Toggle Switches			SIZE 圖紙	A4
1	Ⓐ				TOLERANCE (公差) : 0.00 mm ± 0.25mm 0.0 mm ± 0.40mm ANGULAR : ± 5° FILE NAME : 2ASP0147	DWG NO. 圖 號	2AS3T1A1M2RES			UNIT 單位	inch mm
2	Ⓑ					REV. 版 本	A	DATE 日 期	MAR - 23 - 2006	SHEET 張 數	1 of 1
3	Ⓒ					CHECKED BY 審 核	RICHARD		DRAWN BY 製 圖	ODA	
4	Ⓓ										
5	Ⓔ										

版本 : C

表單編號 : QR-0507