






技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. 额定电压: 250V AC, DC.
3. 耐电压: 800V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 3A AC, DC.

材料

1. 塑胶: PA66 白色

型号	CKT	A	B	C
WAFER-PHB2.0-4PJK-GW	2*2	2.00	7.00	2.90
WAFER-PHB2.0-6PJK-GW	2*3	4.00	9.00	3.10
WAFER-PHB2.0-8PJK-GW	2*4	6.00	11.00	4.30
WAFER-PHB2.0-10PJK-GW	2*5	8.00	13.00	6.30
WAFER-PHB2.0-12PJK-GW	2*6	10.00	15.00	8.30
WAFER-PHB2.0-14PJK-GW	2*7	12.00	17.00	6.30
WAFER-PHB2.0-16PJK-GW	2*8	14.00	19.00	8.30
WAFER-PHB2.0-18PJK-GW	2*9	16.00	21.00	14.30
WAFER-PHB2.0-20PJK-GW	2*10	18.00	23.00	14.30
WAFER-PHB2.0-22PJK-GW	2*11	20.00	25.00	14.30
WAFER-PHB2.0-24PJK-GW	2*12	22.00	27.00	14.30
WAFER-PHB2.0-26PJK-GW	2*13	24.00	29.00	14.30
WAFER-PHB2.0-28PJK-GW	2*14	26.00	31.00	14.30
WAFER-PHB2.0-30PJK-GW	2*15	28.00	33.00	14.30
WAFER-PHB2.0-32PJK-GW	2*16	30.00	35.00	14.30
WAFER-PHB2.0-44PJK-GW	2*22	42.00	47.00	14.30

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES				
DECIMALS:	ANGLES:	TITLE: PHB2.0公头胶壳		
X.X±0.30	X.*±5°	PAR	WAFER-PHB2.0-NPJK-GW	
X.XX±0.25	X.X°±1°	DWN		
X.XXX±0.15		CHKD		
		APVD		
		SCALE:A	UNIT:MM	
		CUSTOMER COPY	SIZE:A4	SHEET:1F1
				REV:A