




ROHS



PCB LAYOUT

SPECIFICATION:

Current Rating : 3AMP

Temperature Range : -40℃to+105℃

Contact Resistance : 20mΩ Max

Insulation Resistance : 1000MΩ Min

Withstanding Voltage : AC 1000V


Material:

Insulator : Polyester (UL94V-0)

Standard: PA9T

Contact: Brass

Plating : Au over Ni



CUSTOMER DRAWING		 深圳市莱联电子有限公司				
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD				
CHECKED						
APPROVED						
TOLERANCES ARE		TITLE	牛角 PIN距2.54 塑高17 双排10PIN 直插	REV.	A	
30-150	±0.35	PART NO.	LAIL-ST-2.54-2X10P-ZC	UNITS	mm	
10-30	±0.2					ANGLE
5-10	±0.15					
0-5	±0.1	±3°				
		DWG. NO.		Projection		