






PIN	A-(mm)	B-(mm)	C-(mm)
1.0-02AWT	1.00	3.50	4.30
1.0-03AWT	2.00	4.50	5.30
1.0-04AWT	3.00	5.50	6.30
1.0-05AWT	4.00	6.50	7.30
1.0-06AWT	5.00	7.50	8.30
1.0-07AWT	6.00	8.50	9.30
1.0-08AWT	7.00	9.50	10.30
1.0-09AWT	8.00	10.50	11.30
1.0-10AWT	9.00	11.50	12.30
1.0-11AWT	10.00	12.50	13.30
1.0-12AWT	11.00	13.50	14.30
1.0-13AWT	12.00	14.50	15.30
1.0-14AWT	13.00	15.50	16.30
1.0-15AWT	14.00	16.50	17.30
1.0-16AWT	15.00	17.50	18.30
1.0-17AWT	16.00	18.50	19.30
1.0-18AWT	17.00	19.50	20.30
1.0-19AWT	18.00	20.50	21.30
1.0-20AWT	19.00	21.50	22.30

- NOTES:
- 1.ELECTRICAL CHARACTERS:
- 1-1.RATING: DC 50V 0.5A;
- 1-2.CONTATCT RESISTANCE:≤20mΩ;
- 1-3.INSULATION RESISTANCE:≥100MΩ DC 500V;
- 1-4.WITHSTANDING VOLTAGE:AC 500V 1min;
- 1-5.OPERATING TEMPERATURE:-25°C~+105°C;

TOLERANCE UNLESS OTHERWISE SPEC		SHENZHEN FUGANG TECHNOLOGY CO.,LTD			
BASIC DIMENSION	TOLERANCE	DSND	B	C	TITLE:1.0 Connector
x.x	±0.50	CHKD	L	P	J
x.xx	±0.30	APVD	L	Z	W
x.xxx	±0.10				
ANGLES	±3°				
②	PIN	1	Phosphor copper	Ni Sn PLATED	Ni0.5-1.5um Sn2.5-3.5um
①	HOUSING	1	PA9T/LCP	Beige	
No.	PART NAME	Q'TY	MATERIAL	REMARK	
	UNIT:mm	SCALE:1:1	SIZE:A4	SHEET:1/1	