

技术指标(Technical Index):

- 1.工作温度(Temperature range): $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$.
- 2.适用线规(Apply to gauge):AWG#28~#22
- 3.额定电压(Rated voltage):250V DC/AC(rms).
- 4.额定电流(Rated current):3.0A AC,DC.
- 5.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 6.耐压值(Dielectricwithstanding voltage):800V AC/minute.
- 7.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.

Part No	Pin	A	B
WAFER-PHD2.0-4PLB	2*2	2.00	6.00
WAFER-PHD2.0-6PLB	2*3	4.00	8.00
WAFER-PHD2.0-8PLB	2*4	6.00	10.00
WAFER-PHD2.0-10PLB	2*5	8.00	12.00
WAFER-PHD2.0-12PLB	2*6	10.00	14.00
WAFER-PHD2.0-14PLB	2*7	12.00	16.00
WAFER-PHD2.0-16PLB	2*8	14.00	18.00
WAFER-PHD2.0-18PLB	2*9	16.00	20.00
WAFER-PHD2.0-20PLB	2*10	18.00	22.00
WAFER-PHD2.0-22PLB	2*11	20.00	24.00
WAFER-PHD2.0-24PLB	2*12	22.00	26.00
WAFER-PHD2.0-26PLB	2*13	24.00	28.00
WAFER-PHD2.0-28PLB	2*14	26.00	30.00
WAFER-PHD2.0-30PLB	2*15	28.00	32.00
WAFER-PHD2.0-32PLB	2*16	30.00	34.00
WAFER-PHD2.0-36PLB	2*18	34.00	38.00
WAFER-PHD2.0-40PLB	2*20	38.00	42.00

序号	品名	材质
①	PHD立贴WTB胶芯	米色 LCP UL94V-0
②	PHD立贴(连续)端子	铜合金/表面镀锡
③	PHD2.0立贴WTB胶盖	米色 LCP UL94V-0

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: 2.0 Pitch D型双排立贴	
DECIMALS:		PAR	WAFER-PHD2.0-NPLB
ANGLES:		DWN	
0.X ± 0.25		CHKD	
0.XX ± 0.12		APVD	
0.XXX ± 0.05		SCALE:1:1	UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1
			REV:A

