








技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$ 。
3. 额定电压: 150V AC/DC。
4. 额定电流: 1.0A AC/DC(AWG#28)。
5. 接触电阻: $\leq 20\text{m}\Omega$ (Initial) per contact, $\leq 40\text{m}\Omega$ Change allowed.
6. 绝缘电阻: $\geq 500\text{M}\Omega$ 。
7. 耐电压: 500V AC (Minute)

型号	CKT	A	B
WAFER-DF1.25-10PLB-GYC	2*5	10.50	5.00
WAFER-DF1.25-12PLB-GYC	2*6	11.75	6.25
WAFER-DF1.25-14PLB-GYC	2*7	13.00	7.50
WAFER-DF1.25-16PLB-GYC	2*8	14.25	8.75
WAFER-DF1.25-18PLB-GYC	2*9	15.50	10.00
WAFER-DF1.25-20PLB-GYC	2*10	16.75	11.25
.....			
WAFER-DF1.25-50PLB-GYC	2*25	(25*1.25)+4.25	(25*1.25)-1.25



PCB.WELDING DRAWING (TOLERANCE:±0.05)



4	1.25A型双排立式吸盖	LCP UL94V-0 本色
3	1.25A型双排立式胶芯	PA6T UL94V-0 本色
2	1.25A型双排立式焊片	黄铜/表面镀锡80u" Min, 镀镍30u"Min
1	1.25A型双排立式端子	黄铜/表面镀锡80u" Min, 镀镍30u"Min
序号	名称	数量

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: 1.25 Pitch A型(DF13)双排立式带柱业务图		
DECIMALS:		PAR		
X.X±0.30		DWN		
X.XX±0.25		CHKD		
X.XXX±0.15		APVD		
ANGLES:		SCALE:A		
X.*±5°		UNIT:MM		
X.X'±1°		SIZE:A4		
		SHEET:1F1		
		REV:A		