





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Current Rating : 3AMP
Temperature Range : -40℃to+105℃
Contact Resistance : 20mΩ Max
Insulation Resistance : 1000MΩ Min
Withstanding Voltage : AC 1000V
Material:
Insulator : Polyester (UL94V-0)
Standard: PA9T
Contact: Brass
Plating : Au over Ni



PCB LAYOUT

CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECKED					
APPROVED		TITLE	牛角 PIN距2.54 塑高17 双排17PIN 直插	REV.	A
TOLERANCES ARE		PART NO.	LAIL-ST-2.54-2X17P-ZC	UNITS	mm
		DWG. NO.		Projection	
		30-150	±0.35	ANGLE	±3°
		10-30	±0.2		
		5-10	±0.15		
		0-5	±0.1		