




ROHS



PCB LAYOUT

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Current Rating : 3AMP

Temperature Range : -40°Cto+105°C

Contact Resistance : 20mΩ Max

Insulation Resistance : 1000MΩ Min

Withstanding Voltage : AC 1000V


Material:

Insulator : Polyester (UL94V-0)

Standard: PA9T

Contact: Brass

Plating : Au over Ni



CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD				
CHECKED							
APPROVED							
TOLERANCES ARE			TITLE		筒牛 PIN距2.0 塑高5.7 双排5PIN 直插	REV.	A
30-150	±0.35	ANGLE	PART NO.		LAIL-SI-2. 0-2X5P-ZC	UNITS	mm
10-30	±0.2						
5-10	±0.15	±3°	DWG. NO.			Projection	
0-5	±0.1						