







ROHS Compliant

MAPX	MODIFICATION	DATE	DRAW	APPROVE
序号	品名	材质		
①	0.8—C型卧式WTB胶芯	LCP UL94 V-0 自然色		
②	0.8—C型立式WTB端子	铜合金/表面镀锡		
③	0.8—C型卧式WTB焊片	铜合金/表面镀锡		



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$.
3. 额定电压: 30V, AC/DC.
4. 耐电压: 200V, AC/minute.
5. 接触电阻: $\leq 0.02\Omega$.
6. 绝缘电阻: $\geq 100\text{M}\Omega$.
7. 额定电流: 0.5A AC/DC.



Part No	CKT	A	B
WAfer-0.8-2PWT	2	0.80	3.80
WAfer-0.8-3PWT	3	1.60	4.60
WAfer-0.8-4PWT	4	2.40	5.40
WAfer-0.8-5PWT	5	3.20	6.20
WAfer-0.8-6PWT	6	4.00	7.00
WAfer-0.8-7PWT	7	4.80	7.80
WAfer-0.8-8PWT	8	5.60	8.60
WAfer-0.8-9PWT	9	6.40	9.40
WAfer-0.8-10PWT	10	7.20	10.20
WAfer-0.8-11PWT	11	8.00	11.00
WAfer-0.8-12PWT	12	8.80	11.80
WAfer-0.8-13PWT	13	9.60	12.60
WAfer-0.8-14PWT	14	10.40	13.40
WAfer-0.8-15PWT	15	11.20	14.20

Part No	CKT	A	B
WAfer-0.8-16PWT	16	12.00	15.00
WAfer-0.8-17PWT	17	12.80	15.80
WAfer-0.8-18PWT	18	13.60	16.60
WAfer-0.8-19PWT	19	14.40	17.40
WAfer-0.8-20PWT	20	15.20	18.20
WAfer-0.8-21PWT	21	16.00	19.00
WAfer-0.8-22PWT	22	16.80	19.80
WAfer-0.8-23PWT	23	17.60	20.60
WAfer-0.8-24PWT	24	18.40	21.40
WAfer-0.8-25PWT	25	19.20	22.20
WAfer-0.8-26PWT	26	20.00	23.00
WAfer-0.8-27PWT	27	20.80	23.80
WAfer-0.8-28PWT	28	21.60	24.60

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: 0.80 Pitch C型卧式WTB	
DECIMALS:		PAR	WAfer-0.8-NPWT
X.:±0.50		DWN	Lucas
X.X:±0.20		CHKD	Ethan
X.XX:±0.10		APVD	Jacob
		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
		CUSTOMER COPY	REV:A