





ROHS



PCB LAYOUT

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Current Rating : 3AMP
Temperature Range : -40℃to+105℃
Contact Resistance : 20mΩ Max
Insulation Resistance : 1000MΩ Min
Withstanding Voltage : AC 1000V
Material:
Insulator : Polyester (UL94V-0)
Standard: PA9T
Contact: Brass
Plating : Au over Ni



CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD				
CHECKED							
APPROVED							
TOLERANCES ARE			TITLE		筒牛 PIN距2.0 塑高5.7 双排4PIN 直插	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-SI-2.0-2X4P-ZC	UNITS	mm	
10-30	±0.2						
5-10	±0.15	±3°	DWG. NO.		Projection		
0-5	±0.1						