




 4.98 ± 0.25  4.03 ± 0.20 4.43 ± 0.20 7.35 ± 0.25  2.00 ± 0.10 2.00 ± 0.10 $DIMA \pm 0.20$

技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. 额定电压: 250V AC, DC.
3. 耐电压: 800V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 3A AC, DC.

材料:

1. 塑胶: PA66 白色

型号	CKT	A	B
WAFER-PHD2.0-4PJK-GW12	2*2	2.00	6.00
WAFER-PHD2.0-6PJK-GW12	2*3	4.00	8.00
WAFER-PHD2.0-8PJK-GW12	2*4	6.00	10.00
WAFER-PHD2.0-10PJK-GW12	2*5	8.00	12.00
WAFER-PHD2.0-12PJK-GW12	2*6	10.00	14.00
WAFER-PHD2.0-14PJK-GW12	2*7	12.00	16.00
WAFER-PHD2.0-16PJK-GW12	2*8	14.00	18.00
WAFER-PHD2.0-18PJK-GW12	2*9	16.00	20.00
WAFER-PHD2.0-20PJK-GW12	2*10	18.00	22.00
WAFER-PHD2.0-22PJK-GW12	2*11	20.00	24.00
WAFER-PHD2.0-24PJK-GW12	2*12	22.00	26.00
WAFER-PHD2.0-26PJK-GW12	2*13	24.00	28.00
WAFER-PHD2.0-28PJK-GW12	2*14	26.00	30.00
WAFER-PHD2.0-30PJK-GW12	2*15	28.00	32.00
WAFER-PHD2.0-32PJK-GW12	2*16	30.00	34.00
WAFER-PHD2.0-34PJK-GW12	2*17	32.00	36.00
WAFER-PHD2.0-36PJK-GW12	2*18	34.00	38.00
WAFER-PHD2.0-38PJK-GW12	2*19	36.00	40.00
WAFER-PHD2.0-40PJK-GW12	2*20	38.00	42.00

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd			
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: PHD2.0公头散壳		
			PAR	WAFER-PHD2.0-NPJK-GW12	
DWN					
CHKD					
APVD					
SCALE:A	UNIT:MM				
DECIMALS:	ANGLES:	CUSTOMER COPY	SIZE:A4	SHEET:1F1	REV:A
X.X±0.30	X.*±5°				
X.XX±0.25	X.X'±1°				
X.XXX±0.15					