

Part No	CKT	A	B
PHD2.0-02-4PZZ	2*2	2.0	6.0
PHD2.0-02-6PZZ	2*3	4.0	8.0
PHD2.0-02-8PZZ	2*4	6.0	10.0
PHD2.0-02-10PZZ	2*5	8.0	12.0
PHD2.0-02-12PZZ	2*6	10.0	14.0
PHD2.0-02-14PZZ	2*7	12.0	16.0
PHD2.0-02-16PZZ	2*8	14.0	18.0
PHD2.0-02-18PZZ	2*9	16.0	20.0
PHD2.0-02-20PZZ	2*10	18.0	22.0
PHD2.0-02-22PZZ	2*11	20.0	24.0
PHD2.0-02-24PZZ	2*12	22.0	26.0
PHD2.0-02-26PZZ	2*13	24.0	28.0
PHD2.0-02-28PZZ	2*14	26.0	30.0
PHD2.0-02-30PZZ	2*15	28.0	32.0
PHD2.0-02-32PZZ	2*16	30.0	34.0
PHD2.0-02-34PZZ	2*17	32.0	36.0
PHD2.0-02-36PZZ	2*18	34.0	38.0
PHD2.0-02-38PZZ	2*19	36.0	40.0
PHD2.0-02-40PZZ	2*20	38.0	42.0

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCES

TITLE:

PHD2.0 双排直插WTB

PAR

PHD2.0-02-NPZZ

DWN

Lucas

CHKD

Ethan

APVD

Jacob


SCALE:1:1

UNIT:MM

SIZE:A4

SHEET:1F1

REV:A



技术指标(Technical Index):

- 1.工作温度(Temperature range):
-40°C~+105°C.
- 2.额定电压(Rated voltage):250V DC/AC(rms).
- 3.额定电流(Rated current):3.0A AC,DC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Dielectricwithstanding voltage):
800V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.

序号	品名	材质
①	PHD2.0直针WTB胶芯	PA66加玻纤
②	PHD2.0直针WTB端子	UL94 V-0 米色
		铜合金/表面镀锡