




ROHS



PCB LAYOUT

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Current Rating : 3AMP

Temperature Range : -40°C to $+105^{\circ}\text{C}$

Contact Resistance : $20\text{m}\Omega$ Max

Insulation Resistance : $1000\text{M}\Omega$ Min

Withstanding Voltage : AC 1000V


Material:

Insulator : Polyester (UL94V-0)

Standard: PA9T

Contact: Brass

Plating : Au over Ni



CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECKED						
APPROVED						
TOLERANCES ARE			TITLE	筒牛 PIN距2.54 塑高8.8 双排3PIN 弯插	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-SI-2.54-2X3P-WC	UNITS	mm
10-30	±0.2		DWG. NO.		Projection	
5-10	±0.15					
0-5	±0.1					