








技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. 额定电压: 150V AC, DC.
3. 耐电压: 500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$ (Initial) per contact, $\leq 40\text{m}\Omega$ Change allowed.
5. 绝缘电阻: $\geq 500\text{M}\Omega$.
6. 额定电流: 1A AC, DC.

材质:

1. 塑胶: PA66 白色



型号	CKT	A	B	C
WAFER-DF1.25-10PJK-GW	2*5	10.50	5.00	7.86
WAFER-DF1.25-12PJK-GW	2*6	11.75	6.25	9.11
WAFER-DF1.25-14PJK-GW	2*7	13.00	7.50	10.36
WAFER-DF1.25-16PJK-GW	2*8	14.25	8.75	11.61
WAFER-DF1.25-18PJK-GW	2*9	15.50	10.00	12.86
WAFER-DF1.25-20PJK-GW	2*10	16.75	11.25	14.11
WAFER-DF1.25-22PJK-GW	2*11	18.00	12.50	15.36
WAFER-DF1.25-24PJK-GW	2*12	19.25	13.75	16.61
WAFER-DF1.25-28PJK-GW	2*14	21.75	16.25	19.11
WAFER-DF1.25-30PJK-GW	2*15	23.00	17.50	20.36
WAFER-DF1.25-32PJK-GW	2*16	24.25	18.75	21.61
WAFER-DF1.25-34PJK-GW	2*17	25.50	20.00	22.86
WAFER-DF1.25-36PJK-GW	2*18	26.75	21.25	24.11
WAFER-DF1.25-38PJK-GW	2*19	28.00	22.50	25.36
WAFER-DF1.25-40PJK-GW	2*20	29.25	23.75	26.61
WAFER-DF1.25-42PJK-GW	2*21	30.50	25.00	27.86
WAFER-DF1.25-44PJK-GW	2*22	31.75	26.25	29.11
WAFER-DF1.25-46PJK-GW	2*23	33.00	27.50	30.36
WAFER-DF1.25-48PJK-GW	2*24	34.25	28.75	31.61
WAFER-DF1.25-50PJK-GW	2*25	35.50	30.00	32.86

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: 1.25 Pitch A型(DF13)双排公头胶壳		
DECIMALS:		PAR		
X.X ±0.30		DWN		
X.XX ±0.25		CHKD		
X.XXX ±0.15		APVD		
ANGLES:		SCALE: A		
X.* ±5°		UNIT: MM		
X.X' ±1°		SIZE: A4		
CUSTOMER COPY		SHEET: 1F1		
		REV: A		