





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:
Current Rating : 3AMP
Temperature Range : -40℃to+105℃
Contact Resistance : 20mΩ Max
Insulation Resistance : 1000MΩ Min
Withstanding Voltage : AC 1000V
Material:
Insulator : Polyester (UL94V-0)
Standard: PA9T
Contact: Brass
Plating : Au over Ni



PCB LAYOUT

CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECKED						
APPROVED						
TOLERANCES ARE			TITLE	牛角 PIN距2.54 塑高17 双排15PIN 直插	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-ST-2.54-2X15P-ZC	UNITS	mm
10-30	±0.2		DWG. NO.		Projection	
5-10	±0.15					
0-5	±0.1					