








技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$ 。
3. 额定电压: 150V AC/DC。
4. 额定电流: 1.0A AC/DC(AWG#28)。
5. 接触电阻: $\leq 20\text{m}\Omega$ (Initial) per contact, $\leq 40\text{m}\Omega$ Change allowed.
6. 绝缘电阻: $\geq 500\text{M}\Omega$ 。
7. 耐压: 500V AC (Minute)

型号	CKT	A	B
WAFER-DF1.25-10PLB-GYR	2*5	12.50	5.00
WAFER-DF1.25-12PLB-GYR	2*6	13.75	6.25
WAFER-DF1.25-14PLB-GYR	2*7	15.00	7.50
WAFER-DF1.25-16PLB-GYR	2*8	16.25	8.75
WAFER-DF1.25-18PLB-GYR	2*9	17.50	10.00
WAFER-DF1.25-20PLB-GYR	2*10	18.75	11.25
.....			
WAFER-DF1.25-50PLB-GYR	2*25	$(25*1.25)+6.25$	$(25*1.25)-1.25$

PCB.WELDING DRAWING (TOLERANCE: ± 0.05)

4	1.25A型双排立式吸盖	LCP UL94V-0 本色
3	1.25A型双排立式胶芯	PA6T UL94V-0 本色
2	1.25A型双排立式焊片	黄铜/表面镀锡80u" Min, 镀镍30u"Min
1	1.25A型双排立式端子	黄铜/表面镀锡80u" Min, 镀镍30u"Min
序号	名称	数量

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 1.25 Pitch A型(DF13)双排立式业务图	
			PAR	WAFER-DF1.25-NPLB-GYR
DECIMALS:	ANGLES:		DWN	
X.X±0.30	X.*±5°		CHKD	
X.XX±0.25	X.X*±1°		APVD	
X.XXX±0.15		CUSTOMER COPY	SCALE:A	UNIT:MM
			SIZE:A4	SHEET:1F1
				REV:A