





SEC:A-A



SEC:B-B



SEC:C-C

## 技术指标(Technical Index):

- 1.工作温度(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$ .
- 2.额定电压(Rated voltage):250V DC/AC.
- 3.额定电流(Rated current):3.0A.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$ .
- 5.耐压值(Dielectricwithstanding voltage):800V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$ .
- 7.适用线规(Apply to gauge):AWG#22~#28.

|                                          |  |         |  |                                                                                                                                                       |  |                              |  |                                                                                       |  |
|------------------------------------------|--|---------|--|-------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------------------------|--|---------------------------------------------------------------------------------------|--|
| 序号                                       |  | 品名      |  | 材质                                                                                                                                                    |  |                              |  |                                                                                       |  |
| 1                                        |  | 端子      |  | Phosphor Bronze<br>Bright tin plated                                                                                                                  |  |                              |  |                                                                                       |  |
| MANUFACTURE DWG                          |  |         |  | <div> 东莞市讯普电子科技有限公司<br/>DongGuan XunPu Electronics Co.,Ltd</div> |  |                              |  |                                                                                       |  |
| UNLESS OTHERWISE<br>SPECIFIED TOLERANCES |  |         |  |                                                                  |  | TITLE:<br>PA2.0(PHD)-WTB公头端子 |  |                                                                                       |  |
|                                          |  |         |  |                                                                                                                                                       |  | PAR      WAFER-PHD2.0-DZ-G   |  |                                                                                       |  |
| DWN      Lucas                           |  |         |  |                                                                                                                                                       |  |                              |  |                                                                                       |  |
| CHKD      Ethan                          |  |         |  |                                                                                                                                                       |  |                              |  |                                                                                       |  |
| APVD      Jacob                          |  |         |  |                                                                                                                                                       |  |                              |  |                                                                                       |  |
| DECIMALS:                                |  | ANGLES: |  | SCALE:1:1                                                                                                                                             |  | UNIT:MM                      |  |  |  |
| X.:±0.50                                 |  | ±1°     |  | CUSTOMER COPY                                                                                                                                         |  | SIZE:A4                      |  | SHEET:1F1                                                                             |  |
| X.X:±0.20                                |  |         |  |                                                                                                                                                       |  |                              |  | REV:A                                                                                 |  |
| X.XX:±0.10                               |  |         |  |                                                                                                                                                       |  |                              |  |                                                                                       |  |