

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Current Rating : 3AMP

Temperature Range : -40℃to+105℃

Contact Resistance : 20mΩ Max

Insulation Resistance : 1000MΩ Min

Withstanding Voltage : AC 1000V




Material:

Insulator : Polyester (UL94V-0)


Standard: PA9T

Contact: Brass

Plating : Au over Ni



PCB LAYOUT



COSTOMER DRAWING			深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING							
CHECKED							
APPROVED							
TOLERANCES ARE							
30-150	±0.35	ANGLE	PART NO.		LAIL-SI-2.54-2X8P-ZC	UNITS	mm
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			±3°	DWG. NO.			
					Projection 		