




SEC:A-A



SEC:B-B



SEC:C-C

技术指标(Technical Index):

- 1.工作温度(Temperature range): $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):30V AC/DC.
- 3.额定电流(Rated current):0.5A AC/DC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Dielectricwithstanding voltage):200V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 100\text{M}\Omega$.
- 7.适用线规(Apply to gauge):AWG#28~#32(O.D0.6mm MAX).

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: 0.80 Pitch C型WTB公头端子
DECIMALS:		PAR
X.:±0.50		DWN
X.X:±0.20		CHKD
X.XX:±0.10		APVD
ANGLES:		SCALE1:1
±1°		UNIT:MM
		SIZE:A4
		SHEET:1F1
		REV:A