





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Current Rating : 3AMP
Temperature Range : -40℃to+105℃
Contact Resistance : 20mΩ Max
Insulation Resistance : 1000MΩ Min
Withstanding Voltage : AC 1000V
Material:
Insulator : Polyester (UL94V-0)
Standard: PA9T
Contact: Brass
Plating : Au over Ni



PCB LAYOUT

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
DRAWING		TITLE 牛角 PIN距2.54 塑高17 双排13PIN 直插		REV.	A	
CHECKED						
APPROVED						
TOLERANCES ARE		ANGLE	PART NO.	LAIL-ST-2.54-2X13P-ZC	UNITS	mm
30-150	±0.35					
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
		±3°	DWG. NO.		Projection	