








Technical Index

1. Temperature range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. Rated voltage: 150V DC/AC.
3. Rated current: 1.0A.
4. Contact resistance:
 $\leq 20\text{m}\Omega$ (Initial) per contact,
 $\leq 40\text{m}\Omega$ Change allowed.
5. Dielectric withstanding voltage: 500V AC/minute.
6. Insulation resistance: $\geq 500\text{M}\Omega$.
7. Apply to gauge: AWG#26~AWG#30. (O.D 1.0mm Max)

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 1.25 Pitch A型(DF13) 双排公头端子	
			PAR	WAFER-DF1.25-DZ-G
DWN				
CHKD				
APVD				
DECIMALS:	ANGLES:	SCALE:A	UNIT:MM	
X.X±0.30	X.*±5°	CUSTOMER COPY	SIZE:A4	SHEET:1F1
X.XX±0.25	X.X'±1°			REV:A
X.XXX±0.15				