




ROHS



PCB LAYOUT

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Current Rating : 3AMP

Temperature Range : -40°Cto+105°C

Contact Resistance : 20mΩ Max

Insulation Resistance : 1000MΩ Min

Withstanding Voltage : AC 1000V


Material:

Insulator : Polyester (UL94V-0)

Standard: PA9T

Contact: Brass

Plating : Au over Ni



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING					
CHECKED					
APPROVED					
TOLERANCES ARE		TITLE	简牛 PIN距2.54 塑高8.9 双排4PIN 直插	REV.	A
30-150	±0.35	PART NO.	LAIL-SI-2.54-2X4P-ZC	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1	DWG. NO.		Projection	
ANGLE					
±3°					