




ROHS


REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Current Rating : 3AMP
Temperature Range : -40℃to+105℃
Contact Resistance : 20mΩ Max
Insulation Resistance : 1000MΩ Min
Withstanding Voltage : AC 1000V
Material:
Insulator : Polyester (UL94V-0)
Standard: PA9T
Contact: Brass
Plating : Au over Ni



PCB LAYOUT



CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECKED						
APPROVED						
TOLERANCES ARE			TITLE	筒牛 PIN距2.54 塑高8.8 双排7PIN 弯插	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-SI-2.54-2X7P-WC	UNITS	mm
10-30	±0.2		DWG. NO.		Projection	
5-10	±0.15					
0-5	±0.1					