






1. **Electrical Characteristics:**
Contact Current Rating: 0.5 Amperes.
Dielectric Withstanding Voltage: AC 500V r.m.s.
Insulation Resistance: 1000 MΩ Minimum.
Contact Resistance: 40 mΩ Maximum.
2. **Environmental:**
Operating Temperature: -25°C ~ +90°C.
3. **Environmental:**
Mating Cycles: 5,000 Insertions.
4. **Mechanical Characteristics:**
Card Push Insertion/Out Force: 0.2 ~ 1.40 kgf.
Contact Separation Force: 0.20 kgf Minimum.
5. **Material:**
Insulator: HI-Temp Plastic UL 94V-0 Rated.
Contact: Copper Alloy (t=0.15mm).
Shell: Stainless Steel (t=0.15mm).
Spring: SWP.




 PAD AREA

 KEEP OUT AREA




RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05

Circuit Diagram for Detect Switch




TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd.							
X.X:±0.35	X.X':±3"	PART NO. TF-01A	TITLE: MICRO SD CARD PUSH PUSH SMT 不镀金 外牌						
X.XX:±0.25	X.XX':±2"								
X.XXX:±0.15									
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG  <table><tr><td>SCALE</td><td>SHEET</td></tr><tr><td>N:A</td><td>1/2</td></tr></table>			SCALE	SHEET	N:A	1/2
SCALE	SHEET								
N:A	1/2								
MATERILA	— — —	CHED: Olivia							
FINISH	— — —	APPD: Ava							

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



纸箱规格:340*340*385

NO.4



NO.3

1. 材质要求:

- 1.1 纸箱的材质为K=K;外形尺寸为34*34*38.5;
- 1.2 卷盘的材质为PS,卷盘的外形尺寸为 $\phi 330 \times 30.4$;
- 1.3 卷带的材质为PS,卷带的外形尺寸为2020*24.00*3.0mm;

2. 包装方式:

- 2.1 将卷带放入包装机后,前空5PCS,后放产品1000PCS,再后空5PCS;上带留300MM长度。
- 2.2 将包装好的产品从包装机上取下并包装好,贴上内盘标签;
- 2.3 把累叠好的12盘叠放入纸箱中共计12Kset,上下放纸板,纸箱四个角塞护角纸;
- 2.4 把包装好的成品打包封箱,并在纸箱外贴上标签

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X:±0.35	X.X':±3"	PART NO. TF-01A	TITLE: MICRO SD CARD PUSH PUSH SMT 不镀金 外牌	
X.XX:±0.25	X.XX':±2"			
X.XXX:±0.15		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm			
MATERILA	---	CHED: Olvia		SCALE
FINISH	---	APPD: Ava		SHEET
			N:A	2/2