




PCB LAYOUT

尺寸(mm)

编号	A	B
A2006-16AW	30.00	34.00

SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
5001-HY0020W-02P1-00-B	2.00	6.00
5001-HY0020W-03P1-00-B	4.00	8.00
5001-HY0020W-04P1-00-B	6.00	10.00
5001-HY0020W-05P1-00-B	8.00	12.00
5001-HY0020W-06P1-00-B	10.00	14.00
5001-HY0020W-07P1-00-B	12.00	16.00
5001-HY0020W-08P1-00-B	14.00	18.00
5001-HY0020W-09P1-00-B	16.00	20.00
5001-HY0020W-10P1-00-B	18.00	22.00
5001-HY0020W-11P1-00-B	20.00	24.00
5001-HY0020W-12P1-00-B	22.00	26.00
5001-HY0020W-20P1-00-B	38.00	42.00

制图 DRAWN	变更内容 DESCRIPTION	日 期 DATE	GENERL TOLERANCE		制 图 DRAWING	JIMI			料 号 PART NO.	5001-HY0020W-**P1-00-B	版 本 REV.	A				
			X.±0.25	X.*±2°	审 核 CHECK		品 名 TITLE	HY弯针 WAFER DIP TYPE	页 次 SHEET	1/1						
											.X±0.20	.X*±1°	核 准 APPROVAL	LOUIS	客户料号 CUTM. NO.	
			.XX±0.15	.XX*±0.5°		LOUIS										
			.XXX±0.10	.XXX*±0.5°	单 位 UNITS	MM	比 例 SCALE	1:1	深圳市文章济美科技有限公司							