






P/N	CKT	A	B	C	D	E
JME123041-602050-HF	20	4.50	9.50	19.45	21.70	21.11
JME123041-603050-HF	30	7.00	12.00	21.95	24.20	23.61
JME123041-604050-HF	40	9.50	14.50	24.45	26.70	26.11
JME123041-605050-HF	50	12.00	17.00	26.95	29.20	28.61
JME123041-606050-HF	60	14.50	19.50	29.45	31.70	31.11
JME123041-608050-HF	80	19.50	24.50	34.45	36.70	36.11
JME123041-600050-HF	100	24.50	29.50	39.45	41.70	41.11
JME123041-600250-HF	120	29.50	34.50	44.45	46.70	46.11

6	Hook	2	Copper Alloy	Under: Ni 50~100u", Tail: Tin 80~150u"
5	Power contact	4	Copper Alloy	Under: Ni 60~200u", Contact: Au 4u" MIN., Tail: Tin 80~150u"
4	Signal contact	Pin number	Copper Alloy	Under: Ni 60~200u", Contact: Au 4u" MIN., Tail: Au 2u" MIN.
3	Cap	1	Polyamide, UL94V-0, Black	N/A
2	Insulator	1	Polyamide, UL94V-0, Black	N/A
1	Guide	1	Polyamide, UL94V-0, Black	N/A
NO.	Part name	Quantity	Material	Plating

				UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
				X. ±0.20
				X.X ±0.10
				X.XXX ANG. ±0°30'
△	Correction update	QF.DONG	2022-10-27	
△	Dimension update	QF.DONG	2022-10-10	
	Official release.	QF.DONG	2022-08-01	
SER	REVISIONS	CHK	DATE	UNIT
				MM

客户图 Drawings	东莞市文章济美电子有限公司			
APPROVED TS Chen	DATE 2022-08-01	COMPUTER NO JME123041-60XX50-HF		
CHECKED QF DONG	DATE 2022-08-01	NAME BTB0.5-A REC (THR TYPE) Page 1/2		
DRAWN Kuan He	DATE 2022-08-01	SIZE A4	SCALE 2:1	REV D



Recommended land pattern dimension of PCB
(PCB thickness: T=1.6mm)

				UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		客户图 Drawings		东莞市文章济美电子有限公司			
				X.		APPROVED		DATE		COMPUTER NO	
				X.X	±0.20	TS Chen		2022-08-01		JME123041-60XX50-HF	
				X.XX	±0.10	CHECKED		DATE		NAME	
				X.XXX		QF DONG		2022-08-01		BTB0.5-5A REC (THR TYPE) Page 2/2	
				ANG.	±0°30'	DRAWN		DATE		SIZE	
				UNIT		Kuan He		2022-08-01		SCALE	
SER	REVISIONS	CHK	DATE	MM						A4	REV
4		5		6		7		8		9	

