




ROHS



PCB LAYOUT

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Current Rating : 3AMP

Temperature Range : -40°Cto+105°C

Contact Resistance : 20mΩ Max

Insulation Resistance : 1000MΩ Min

Withstanding Voltage : AC 1000V


Material:

Insulator : Polyester (UL94V-0)

Standard: PA9T

Contact: Brass

Plating : Au over Ni



CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司					
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD					
CHECKED								
APPROVED								
TOLERANCES ARE			TITLE		筒牛 PIN距2.0 塑高5.7 双排7PIN 直插		REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-SI-2.0-2X7P-ZC	UNITS	mm	Projection	
10-30	±0.2							
5-10	±0.15							
0-5	±0.1							
			DWG. NO.					