




规格 65600001009.J

文件号 A-2025-65600001009.J

版本1

Shape and Size (mm)



Electrical Performance

Model	For Fuse	Rated Ampere	Rated Voltage	Voltage Drop	Insulation Resistance	Dielectric Strength
65600001009.J	5*20	10A	250V	<20mV	>100mΩ	>2000Vac

Package and Material

Insulating Body	Contacts	Flame Retardant Grade	Package
PA66	Copper nickel plating	UL94V0	100Pcs/Bag

Soldering Methods

Soldering Methods	Solderability
Wave Soldering	245°C,3s ACC. to IEC 60068-2-20 Resistance to soldering heat 260°C,10s ACC.to IEC 60068-2-20