






ROHS



PCB LAYOUT

Remarks:

Material:

1-1. Body: PBT, Black, RoHS

1-2. Terminal: Brass, T=0.25±0.01

(Surface treatment: Overall nickel plating 50μ"; Welding area tin plating 100μ"; Contact area gold plating G/FU)

1-3. Housing: Iron SPCC, T=0.3mm, Nickel plating 50μ" MIN.

Electrical Test:

2-1. Contact Resistance: 30 MILLI OHMS MAX

2-2. Insulation Resistance: 100 MEGA OHMS MIN

2-3. Withstand Voltage: 500V AC ONE MIN LEVEL

2-4. Operating Temperature: -20°C ~ 85°C

All materials used must comply with RoHS standards.

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	USB连接器Type-A 4PIN-弯插L14.2(直口)	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-TYPE-A-4P-03-WC	UNITS	mm
10-30	±0.2		DWG.NO.			
5-10	±0.15					
0-5	±0.1					
			Projection 			